
LABEL APPLICATOR A P Series






A Mech-Sensor combines with a sensor that automatically detects labels of different strokes to eliminate the need for manual alignment when you load labels.

- For pre-printed general roll labels. No special (punched or slit) labels or separators required.
- Supports use of label size from 18x20mm up to 60x100mm.






MODEL	LABEL	LABEL S	IZE(mm)	MAX. OOTSIDE DIAMETER(mm)
MODEL	GAP(mm)	STROKE	WIDTH	
APN-30			20-30	
APN-60	2-3	18-60	25-60	100
APN-100			50-100	

The Mech-Sensor

catches the label and automatically detects the stroke for smooth





A new slidable Mech-Sensor provides support for round, oval, and other non-rectangular shape labels.

- For eye-catching labels of various shapes that appeal to customers.
- Supports use of the label size from 20 x 20mm up to 60 x 100mm. For pre-printed general roll labels. No special (punched or slit) labels or separators required.








to the left or right until it is in the center of the label.

MODEL	LABEL	LABEL SIZE(mm)		MAX. OOTSIDE
MODEL	GAP(mm)	STROKE	WIDTH	DIAMETER(mm
APF-30	2-3	20-60	20-30	100
APF-60			20-60	
APF-100		20-100		





APN10-30


The smaller the label it is when you dispense, the more troublesome it becomes.....

The new type of a premium tool. APN10-30 assures high performance for samll labels.

- For pre-printed general roll labels. No special (punched or slit) labels or separators required.
- Supports use of label size from 10x30mm up to 60x30mm.

1	MODEL	LABEL GAP(mm)	LABEL SIZE(mm)		MAX. OOTSIDE
			STROKE	WIDTH	DIAMETER(mm
	APN10-30	2-3	10-60	20-30	100

Notice



- Some types of film, synthetic paper, and other special labels may not be supported.
- Please ask our distributor for details before using special labels.
- We reserve the right to change specifications without notice for improvement.

OJP PAT. 2708677, 2708680

TOWA CO.,LTD.

Ginza YK Bldg., #10-9, Ginza 5-chome, Chuo-ku, Tokyo 104-0061, Japan Tel:+81-3-3572-9621 Fax:+81-3-3572-9620 http://www.towa.jp/export/ e-mail: export@towa-ltd.co.jp